

# 1437MSSC Cut Sheet



Hammond pushbutton enclosure, 3 holes, 22mm, NEMA 4/4X, 8 x 4 x 5in (HxWxD), wall mount, 304 stainless steel, #4 brush finish, hinged screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1437MSSC>

## Technical Specifications

<b>Brand</b>	Hammond
<b>Item</b>	Pushbutton enclosure
<b>Number of Pushbutton Holes</b>	3 holes
<b>Pushbutton Hole Nominal Size</b>	22mm
<b>Slope Top</b>	No
<b>NEMA Rating</b>	4/4X
<b>IP Rating</b>	IP68
<b>Nominal Enclosure Dimensions</b>	8 x 4 x 5in (HxWxD)
<b>Enclosure Height</b>	8.31in
<b>Enclosure Width</b>	4.31in
<b>Enclosure Depth</b>	4.92in

<b>Mounting</b>	Wall
<b>Integral Mounting Feet</b>	Yes
<b>Integral Mounting Flange</b>	No
<b>Dual Access</b>	No
<b>Knockouts</b>	No
<b>Material</b>	304 stainless steel
<b>Finish</b>	#4 brush
<b>Cover Type</b>	Hinged screw cover
<b>Hinge Type</b>	Internal lift-off hinge
<b>Number of Hinges Per Door</b>	2
<b>Additional Information</b>	Extra deep

## Agency Approvals

<b>UL Listed File #</b>	E65324
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	LR21001
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>