

# 1444050000 Cut Sheet



Weidmuller wire crimping tool, self-adjusting, rotatable die, trapezoidal profile, 26–10 AWG capacity, compatible with insulated and non-insulated wire ferrules, locking die position.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1444050000>

---

## Technical Specifications

<b>Brand</b>	Weidmuller
<b>Item</b>	Wire crimping tool
<b>Self-adjusting</b>	Yes
<b>Rotatable Die</b>	Yes
<b>Crimp Profile</b>	Trapezoidal
<b>Crimp Length</b>	0.57in (14.5mm)
<b>Capacity</b>	26–10 AWG
<b>Compatible Connector</b>	Insulated and non-insulated wire ferrules
<b>Tool Features</b>	Locking die position
<b>Handle Type</b>	Plastic coated handles
<b>Overall Length</b>	7.9in (200mm)

---

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>