

# 1447SE12HK Cut Sheet



Hammond disconnect enclosure, NEMA 4/12/13, right flange, 30 x 25 x 12in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, single-door, 2-point padlocking handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1447SE12HK>

## Technical Specifications

|                                     |                        |
|-------------------------------------|------------------------|
| <b>Brand</b>                        | Hammond                |
| <b>Item</b>                         | Disconnect enclosure   |
| <b>Slope Top</b>                    | No                     |
| <b>Vented</b>                       | No                     |
| <b>NEMA Rating</b>                  | 4/12/13                |
| <b>IP Rating</b>                    | IP66                   |
| <b>Disconnect Mounting</b>          | Right flange           |
| <b>Nominal Enclosure Dimensions</b> | 30 x 25 x 12in (HxWxD) |
| <b>Enclosure Height</b>             | 30.00in                |
| <b>Enclosure Width</b>              | 25.38in                |
| <b>Enclosure Depth</b>              | 12.88in                |
| <b>Mounting</b>                     | Wall                   |

|                                  |                           |
|----------------------------------|---------------------------|
| <b>Integral Mounting Feet</b>    | Yes                       |
| <b>Material</b>                  | Carbon steel              |
| <b>Color</b>                     | ANSI 61 gray              |
| <b>Finish</b>                    | Powder coat               |
| <b>Cover Type</b>                | Single-door               |
| <b>Hinge Type</b>                | Continuous hinge          |
| <b>Number of Hinges Per Door</b> | 1                         |
| <b>Latch Type</b>                | 2-point padlocking handle |
| <b>Padlockable</b>               | Yes                       |
| <b>Keylocking</b>                | No                        |
| <b>Subpanel</b>                  | Subpanel included         |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E65324                                 |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | LR21001                                |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/1447SE12HK.pdf>  
See store item page for other formats.