

1447SF8HK Cut Sheet



Hammond disconnect enclosure, NEMA 4/12/13, right flange, 36 x 25 x 8in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, single-door, 2-point padlocking handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1447SF8HK>

Technical Specifications

Brand	Hammond
Item	Disconnect enclosure
Slope Top	No
Vented	No
NEMA Rating	4/12/13
IP Rating	IP66
Disconnect Mounting	Right flange
Nominal Enclosure Dimensions	36 x 25 x 8in (HxWxD)
Enclosure Height	36.00in
Enclosure Width	25.34in
Enclosure Depth	8.88in
Mounting	Wall

Integral Mounting Feet	Yes
Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	Single-door
Hinge Type	Continuous hinge
Number of Hinges Per Door	1
Latch Type	2-point padlocking handle
Padlockable	Yes
Keylocking	No
Subpanel	Subpanel included

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR21001
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/1447SF8HK.pdf>
See store item page for other formats.