

# 1447SG12HK Cut Sheet



Hammond disconnect enclosure, NEMA 4/12/13, right flange, 36 x 31 x 12in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, single-door, 2-point padlocking handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1447SG12HK>

## Technical Specifications

<b>Brand</b>	Hammond
<b>Item</b>	Disconnect enclosure
<b>Slope Top</b>	No
<b>NEMA Rating</b>	4/12/13
<b>IP Rating</b>	IP66
<b>Disconnect Mounting</b>	Right flange
<b>Nominal Enclosure Dimensions</b>	36 x 31 x 12in (HxWxD)
<b>Enclosure Height</b>	36.00in
<b>Enclosure Width</b>	31.34in
<b>Enclosure Depth</b>	12.88in
<b>Mounting</b>	Wall
<b>Integral Mounting Feet</b>	Yes
<b>Integral Mounting Flange</b>	No
<b>Dual Access</b>	No

<b>Knockouts</b>	No
<b>Material</b>	Carbon steel
<b>Color</b>	ANSI 61 gray
<b>Finish</b>	Powder coat
<b>Cover Type</b>	Single-door
<b>Hinge Type</b>	Continuous hinge
<b>Number of Hinges Per Door</b>	1
<b>Latch Type</b>	2-point padlocking handle
<b>Padlockable</b>	Yes
<b>Keylocking</b>	No
<b>Subpanel</b>	Subpanel included
<b>Additional Information</b>	Purchase operating mechanism, disconnect switch or circuit breaker, and operating handle from disconnect supplier

## Agency Approvals

<b>UL Listed File #</b>	E65324
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	LR21001
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>