

1447SN4G8 Cut Sheet



Hammond disconnect enclosure, NEMA 3R/4/12, right flange, 36 x 31 x 8in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, single-door, stainless steel clamps.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1447SN4G8>

Technical Specifications

Brand	Hammond
Item	Disconnect enclosure
Slope Top	No
NEMA Rating	3R/4/12
IP Rating	IP66
Disconnect Mounting	Right flange
Nominal Enclosure Dimensions	36 x 31 x 8in (HxWxD)
Enclosure Height	36.00in
Enclosure Width	31.38in
Enclosure Depth	9.19in
Mounting	Wall
Integral Mounting Feet	Yes
Integral Mounting Flange	No
Dual Access	No

Knockouts	No
Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	Single-door
Hinge Type	Continuous hinge
Number of Hinges Per Door	1
Latch Type	Stainless steel clamps
Padlockable	No
Keylocking	No
Subpanel	Subpanel included
Additional Information	Purchase operating mechanism, disconnect switch or circuit breaker, and operating handle from disconnect supplier

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR21001
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document