

1471C36 Cut Sheet



Hammond operator console, NEMA 12, 48 x 36 x 18in (HxWxD), freestanding, carbon steel, ANSI 61 gray, powder coat finish, single-door, 3-point keylocking handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1471C36>

Technical Specifications

Brand	Hammond
Item	Operator console
Subpanel	(3) subpanels included
Slope Top	No
NEMA Rating	12
IP Rating	IP54
Nominal Enclosure Dimensions	48 x 36 x 18in (HxWxD)
Enclosure Height	48.00in
Enclosure Width	36.00in
Enclosure Depth	18.15in
Mounting	Freestanding
Dual Access	No
Knockouts	No
Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	Single-door
Hinge Type	Continuous hinge
Number of Lid Hinges	1
Latch Type	3-point keylocking handle
Number of Door Latches	1
Padlockable	No
Keylocking	Yes

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR21001
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document