

# 1481SDH1624 Cut Sheet



Hammond universal deep-hinged door, NEMA 4/12, 14.19 x 20.14 x 2.75in, carbon steel, ANSI 61 gray, concealed hinges. For use with wall-mount enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1481SDH1624>

## Technical Specifications

<b>Brand</b>	Hammond
<b>Item</b>	Universal deep-hinged door
<b>NEMA Rating</b>	4/12
<b>Door Size</b>	14.19 x 20.14 x 2.75in
<b>Door Material</b>	Carbon steel
<b>Hinge Type</b>	Concealed hinges
<b>Color</b>	ANSI 61 gray
<b>Finish</b>	Powder coat
<b>Cutout Size</b>	11.19 x 17.14in
<b>Number of Hinges Per Door</b>	2
<b>Latch Type</b>	1/4-turn semi-flush oil-tight latch
<b>Gasket Type</b>	Oil-resistant neoprene
<b>For Use With</b>	Wall-mount enclosures

## Agency Approvals

<b>UL Listed File #</b>	E65324
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CSA File #</b>	LL21312
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>