

1481WDH1418 Cut Sheet



Hammond universal deep-hinged door, NEMA 4/12, 12.19 x 14.56 x 2.75in, carbon steel, ANSI 61 gray, concealed hinges, polycarbonate window. For use with wall-mount enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1481WDH1418>

Technical Specifications

Brand	Hammond
Item	Universal deep-hinged door
NEMA Rating	4/12
Door Size	12.19 x 14.56 x 2.75in
Door Material	Carbon steel
Hinge Type	Concealed hinges
Color	ANSI 61 gray
Finish	Powder coat

Cutout Size	9.19 x 11.56in
Number of Hinges Per Door	2
Latch Type	1/4-turn semi-flush oil-tight latch
Gasket Type	Oil-resistant neoprene
Window Material	Polycarbonate
Window Size	8.00 x 9.17in
For Use With	Wall-mount enclosures

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	LL21312
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/1481WDH1418.pdf>
See store item page for other formats.