

1481WN4SS1711 Cut Sheet



Hammond enclosure window, 17.00 x 11.00in window, UV-resistant polycarbonate, 19.63 x 13.63in frame, 304 stainless steel, #4 brush finish, oil-resistant neoprene gasket. For use with NEMA 4X enclosures. Mounting hardware included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1481WN4SS1711>

Technical Specifications

Brand	Hammond
Item	Enclosure window
Window Size	17.00 x 11.00in
Window Material	UV-resistant polycarbonate
Frame Size	19.63 x 13.63in
Frame Material	304 stainless steel
Finish	#4 brush
Gasket Type	Oil-resistant neoprene
Cutout Size	18.69 x 12.69in
For Use With	NEMA 4X enclosures
Includes	Mounting hardware

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	LL21312
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/1481WN4SS1711.pdf>
See store item page for other formats.