

# 1481WN4SS2919 Cut Sheet



Hammond enclosure window, 29.00 x 19.00in window, UV-resistant polycarbonate, 31.63 x 21.63in frame, 304 stainless steel, #4 brush finish, oil-resistant neoprene gasket. For use with NEMA 4X enclosures. Mounting hardware included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1481WN4SS2919>

## Technical Specifications

<b>Brand</b>	Hammond
<b>Item</b>	Enclosure window
<b>Window Size</b>	29.00 x 19.00in
<b>Window Material</b>	UV-resistant polycarbonate
<b>Frame Size</b>	31.63 x 21.63in
<b>Frame Material</b>	304 stainless steel
<b>Finish</b>	#4 brush
<b>Gasket Type</b>	Oil-resistant neoprene
<b>Cutout Size</b>	30.69 x 20.69in
<b>For Use With</b>	NEMA 4X enclosures
<b>Includes</b>	Mounting hardware

## Agency Approvals

<b>UL Listed File #</b>	E65324
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CSA File #</b>	LL21312
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>