

# 1485ETQ Cut Sheet



Hammond lay-in wireway fitting, tee, 8 x 8in, outside opening, carbon steel, ANSI 61 gray, quick-release clamps, NEMA 12.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1485ETQ>

## Technical Specifications

|                     |                                 |
|---------------------|---------------------------------|
| <b>Brand</b>        | Hammond                         |
| <b>Item</b>         | Wireway fitting                 |
| <b>Fitting Type</b> | Tee                             |
| <b>Wireway Type</b> | Lay-in                          |
| <b>Size</b>         | 8 x 8in                         |
| <b>Opening</b>      | Outside                         |
| <b>Material</b>     | Carbon steel                    |
| <b>Color</b>        | ANSI 61 gray                    |
| <b>Finish</b>       | Powder coat                     |
| <b>Cover Type</b>   | Hinged                          |
| <b>Latch Type</b>   | Quick-release clamps            |
| <b>NEMA Rating</b>  | 12                              |
| <b>IP Rating</b>    | IP54                            |
| <b>Includes</b>     | (2) snap-on flat sealing plates |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E186830  |
| <b>UL Recognized File #</b> | None   |
| <b>UL Hazardous File #</b>  | None   |
| <b>CSA File #</b>           | LL21312  |
| <b>RoHS Status</b>          | Meets RoHS Chemical Restrictions -<br>No CE (See RoHS Statement Below) |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a>                                 |
| <b>Other</b>                | <a href="#">RoHS Statement</a>   |