

1486B24SS Cut Sheet



Hammond wiring trough, 2.5 x 2.5 x 24in (HxDxL), NEMA 1/4/4X/12, 304 stainless steel, #4 brush finish, single-door.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1486B24SS>

Technical Specifications

Brand	Hammond
Item	Wiring trough
NEMA Rating	1/4/4X/12
IP Rating	IP66
Nominal Enclosure Dimensions	3 x 24 x 3in (HxWxD)
Enclosure Height	2.88in
Enclosure Depth	2.67in
Enclosure Length	24.38in

Integral Mounting Feet	Yes
Knockouts	No
Material	304 stainless steel
Finish	#4 brush
Cover Type	Single-door
Latch Type	Screw clamps
Padlockable	No

Agency Approvals

UL Listed File #	E186830
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	LL21312
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/1486B24SS.pdf>
See store item page for other formats.