

1486D12SS Cut Sheet



Hammond wiring trough, 6 x 6 x 12in (HxDxL), NEMA 1/4/4X/12, 304 stainless steel, #4 brush finish, single-door.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1486D12SS>

Technical Specifications

Brand	Hammond
Item	Wiring trough
NEMA Rating	1/4/4X/12
IP Rating	IP66
Nominal Enclosure Dimensions	6 x 12 x 6in (HxWxD)
Enclosure Height	6.38in
Enclosure Depth	6.17in
Enclosure Length	12.38in
Integral Mounting Feet	Yes
Knockouts	No
Material	304 stainless steel
Finish	#4 brush
Cover Type	Single-door
Latch Type	Screw clamps
Padlockable	No

Agency Approvals

UL Listed File #	E186830
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	LL21312
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement