

1486D36 Cut Sheet

Hammond wiring trough, 6 x 6 x 36in (HxDxL), NEMA 1/4/12, carbon steel, ANSI 61 gray, powder coat finish, single-door.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1486D36>

Technical Specifications

| | |
|-------------------------------------|----------------------|
| Brand | Hammond |
| Item | Wiring trough |
| NEMA Rating | 1/4/12 |
| IP Rating | IP54 |
| Nominal Enclosure Dimensions | 6 x 36 x 6in (HxWxD) |
| Enclosure Height | 6.38in |
| Enclosure Depth | 6.17in |
| Enclosure Length | 36.38in |
| Knockouts | No |
| Material | Carbon steel |
| Color | ANSI 61 gray |
| Finish | Powder coat |
| Cover Type | Single-door |
| Latch Type | Screw clamps |
| Padlockable | No |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | E186830 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CSA File # | LR21312 |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |