

1486E12 Cut Sheet



Hammond wiring trough, 8 x 8 x 12in (HxDxL), NEMA 1/4/12, carbon steel, ANSI 61 gray, powder coat finish, single-door.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1486E12>

Technical Specifications

| | |
|-------------------------------------|----------------------|
| Brand | Hammond |
| Item | Wiring trough |
| NEMA Rating | 1/4/12 |
| IP Rating | IP66 |
| Nominal Enclosure Dimensions | 8 x 12 x 8in (HxWxD) |
| Enclosure Height | 8.38in |
| Enclosure Depth | 8.17in |
| Enclosure Length | 12.38in |

| | |
|-------------------------------|--------------|
| Integral Mounting Feet | Yes |
| Knockouts | No |
| Material | Carbon steel |
| Color | ANSI 61 gray |
| Finish | Powder coat |
| Cover Type | Single-door |
| Latch Type | Screw clamps |
| Padlockable | No |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | E186830 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CSA File # | LL21312 |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/1486E12.pdf>
See store item page for other formats.