

1486E60 Cut Sheet

Hammond wiring trough, 8 x 8 x 60in (HxDxL), NEMA 1/4/12, carbon steel, ANSI 61 gray, powder coat finish, single-door.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1486E60>

Technical Specifications

Brand	Hammond
Item	Wiring trough
NEMA Rating	1/4/12
IP Rating	IP66
Nominal Enclosure Dimensions	8 x 60 x 8in (HxWxD)
Enclosure Height	8.38in
Enclosure Depth	8.17in
Enclosure Length	60.38in
Integral Mounting Feet	Yes
Knockouts	No
Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	Single-door
Latch Type	Screw clamps
Padlockable	No

Agency Approvals

UL Listed File #	E186830
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	LL21312
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement