

1488LN13 Cut Sheet



Hammond operator console, NEMA 12/13, 18 x 24 x 13in (HxWxD), desktop or pedestal mount, carbon steel, ANSI 61 gray, powder coat finish, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1488LN13>

Technical Specifications

Brand	Hammond
Item	Operator console
Slope Top	No
NEMA Rating	12/13
IP Rating	IP54
Nominal Enclosure Dimensions	18 x 24 x 13in (HxWxD)
Enclosure Height	18.44in
Enclosure Width	24.34in
Enclosure Depth	13.37in
Mounting	Desktop or pedestal
Integral Mounting Feet	No
Integral Mounting Flange	No
Dual Access	No
Knockouts	No
Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	Screw cover
Hinge Type	Continuous hinge
Number of Lid Hinges	1
Additional Information	Purchase pedestal column separately

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR21001
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document