

1489P30 Cut Sheet



Hammond pushbutton enclosure, 30 holes, 30mm, NEMA 12, 18 x 14 x 6in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, hinged screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1489P30>

Technical Specifications

| | |
|-------------------------------------|-----------------------|
| Brand | Hammond |
| Item | Pushbutton enclosure |
| Number of Pushbutton Holes | 30 holes |
| Pushbutton Hole Nominal Size | 30mm |
| Slope Top | No |
| NEMA Rating | 12 |
| IP Rating | IP54 |
| Nominal Enclosure Dimensions | 18 x 14 x 6in (HxWxD) |
| Enclosure Height | 17.56in |
| Enclosure Width | 14.31in |
| Enclosure Depth | 6.17in |

| | |
|----------------------------------|--------------------|
| Mounting | Wall |
| Integral Mounting Feet | Yes |
| Integral Mounting Flange | No |
| Dual Access | No |
| Knockouts | No |
| Material | Carbon steel |
| Color | ANSI 61 gray |
| Finish | Powder coat |
| Cover Type | Hinged screw cover |
| Hinge Type | Continuous hinge |
| Number of Hinges Per Door | 1 |
| Subpanel | Subpanel included |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E65324 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | LR21001 |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |