

# 1501-1469 Cut Sheet



ASO Safety Solutions safety contact edge, 15 x 10mm, 3ft length, pigtail, 8.2ft/2.5m cable length. Aluminum mounting rail included. Preassembled with 8.2k ohm resistor for 2-wire installation.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1501-1469>

## Technical Specifications

|                                 |   |
|---------------------------------|---|
| <b>Brand</b>                    | ASO Safety Solutions  |
| <b>Item</b>                     | Safety contact edge   |
| <b>Size</b>                     | 15 x 10mm   |
| <b>Length</b>                   | 3ft   |
| <b>Actuation Force</b>          | 42.9N   |
| <b>Switching Cycles</b>         | >10,000 cycles  |
| <b>Operating Voltage</b>        | 24 VAC/VDC  |
| <b>Contact Surface Material</b> | TPE   |
| <b>Operating Temperature</b>    | 0 to 50 deg C   |
| <b>Connection</b>               | Pigtail   |
| <b>Cable Length</b>             | 8.2ft/2.5m  |
| <b>Conductor Size</b>           | 22 AWG  |
| <b>Includes</b>                 | Aluminum mounting rail                                      |
| <b>Additional Information</b>   | Preassembled with 8.2k ohm resistor for 2-wire installation |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Recognized File #</b> | E341185                                |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |