

# 15010055 Cut Sheet



WERMA audible alarm buzzer, 80 dB at 1m, 2.8 kHz tone frequency, continuous tone(s), 24 VDC, permanent LED indicator(s), red, 22mm, panel mount, polycarbonate housing, red, IP65.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/15010055>

## Technical Specifications

<b>Brand</b>	WERMA
<b>Item</b>	Audible alarm buzzer
<b>Loudness Decibel</b>	80 dB at 1m
<b>Tone Frequency</b>	2.8 kHz
<b>Tone Type</b>	Continuous
<b>Touch to Acknowledge</b>	No
<b>Voltage Rating</b>	24 VDC
<b>Indicator</b>	Permanent LED
<b>Light Color(s)</b>	Red
<b>Barrel Size</b>	22mm
<b>Mounting</b>	Panel
<b>Housing Material</b>	Polycarbonate
<b>Color</b>	Red
<b>IP Rating</b>	IP65

## Agency Approvals

<b>UL Listed File #</b>	E164155
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/15010055.pdf>  
See store item page for other formats.