

151201 Cut Sheet



FATH swivel foot threaded rod, silver, M8-1.25 x 40mm, zinc plated steel, ball joint size 15. For use with all rails. Requires ball joint size 15 swivel base and M8-1.25 thread transport/base plate. Manufacturer part number: 098DM08040M.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/151201>

Technical Specifications

Brand	FATH
Item	Swivel foot threaded rod
Series	10 Series, 15 Series, 30 Series, 40 Series and 45 Series
Color	Silver
Thread Size	M8-1.25 x 40mm
Material	Zinc plated steel
Load Rating	772 lb/350 kg
Ball Joint Size	15
For Use With	All rails
Requires	Ball joint size 15 swivel base and M8-1.25 thread transport/base plate
Manufacturer Part Number	098DM08040M

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement