

151SL44 Cut Sheet



Megapro SHAFTLOK multi-bit screwdriver, 8 pieces, palm-saver with bit storage, 2.6in (66mm) shaft length, Phillips, Torx, square and slotted.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/151SL44>

Technical Specifications

| | |
|-------------------------|----------------------------|
| Brand | Megapro |
| Series | SHAFTLOK |
| Item | Screwdriver |
| Screwdriver Type | Multi-bit |
| Number of Pieces | 8 |
| Ratcheting | No |
| Insulated | No |
| Lock Mechanism | SHAFTLOK and ballpoint bit |
| Overall Length | 8.8in (224mm) |
| Shaft Length | 2.6in (66mm) |

| | |
|-----------------------|--|
| Shaft Diameter | 0.38in (9.7mm) |
| Handle Length | 6.1in (155mm) |
| Handle Type | Palm-saver with bit storage |
| Tip Type | Phillips, Torx, square and slotted |
| Includes | (1) SHAFTLOK handle with bit storage, (1) slotted bit (4, 6mm), (1) Phillips bit (#0, #3), (1) Phillips bit (#1, #2), (1) square bit (#0, #3), (1) square/Robertson bit (#1, #2), (1) Torx bit (T10, T15), (1) Torx bit (T20, T25) |
| Application | Screwdriving |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |