

154-00024 Cut Sheet



Shaviv Mango II deburring tool set, 21 pieces, B10, B20, B30, B50, B60, B70, C40, C42, D80C, E100, E200, E300, E350, E600 and F20, for deburring straight edges, hole edges, cross-hole both edges, hole back-edge, hole inner surface, sheets and flat surface.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/154-00024>

Technical Specifications

Brand	Shaviv
Item	Deburring tool set
Series	Mango II
Number of Pieces	21
Ratcheting	No
Deburring Blade Manufacturer Number	B10, B20, B30, B50, B60, B70, C40, C42, D80C, E100, E200, E300, E350, E600 and F20
For Deburring	Straight edges, hole edges, cross-hole both edges, hole back-edge, hole inner surface, sheets and flat surface
Application	Deburring

For Use On	Steel, aluminum, copper, plastic, brass, cast iron, stainless steel and wood
Package Type	Plastic carrying case
Set Includes	Includes ergonomic universal handle, (5) extendable blade holders (B, C, D, E, F), (15) deburring blades (B10, B20, B30, B50, B60, B70, E100, E200, E300, E350, E600, C40, C42, D80C, F20, plastic carrying case
Additional Information	All-around deburring kit for your workshop. you get all the tools you need for 1000+ applications

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement