

# 154-00054 Cut Sheet



Shaviv Mango II deburring tool set, 7 pieces, E100, E111, E400 and F12, for deburring straight edges and hole edges, rotating and chamfering blade, plastic case.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/154-00054>

## Technical Specifications

<b>Brand</b>	Shaviv
<b>Item</b>	Deburring tool set
<b>Series</b>	Mango II
<b>Number of Pieces</b>	7
<b>Blade Type</b>	Rotating and chamfering
<b>Ratcheting</b>	No
<b>Deburring Blade Manufacturer Number</b>	E100, E111, E400 and F12
<b>For Deburring</b>	Straight edges and hole edges
<b>Cutting Direction</b>	Neutral and right hand
<b>Application</b>	Deburring

<b>For Use On</b>	Steel, aluminum, copper, plastic, brass, cast iron, stainless steel and wood
<b>Package Type</b>	Plastic case
<b>Set Includes</b>	Includes ergonomic universal handle, compact E-type handle, extendable blade holder (F), (4) deburring blades (E100, E111, E400, F12), plastic case
<b>Additional Information</b>	Essential deburring tools for electricians. F12 blade for deburring inside diameter up to 0.47in (12mm). E111 blade for small hole deburring down to 0.06in (1.5mm). E400 scraper blade for inside surface cleanup

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>