

154-90085 Cut Sheet



Shaviv Mango II deburring tool set, 12 pieces, B10, B20, B30, B50, B60, C40, E100 and E300, for deburring straight edges, hole edges, cross-hole both edges, hole back-edge, hole inner surface and flat surface, rotating blade, plastic carrying case.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/154-90085>

Technical Specifications

Brand	Shaviv
Item	Deburring tool set
Series	Mango II
Number of Pieces	12
Blade Type	Rotating
Ratcheting	No
Deburring Blade Manufacturer Number	B10, B20, B30, B50, B60, C40, E100 and E300
For Deburring	Straight edges, hole edges, cross-hole both edges, hole back-edge, hole inner surface and flat surface
Cutting Direction	Neutral and right hand

Application	Deburring
For Use On	Steel, aluminum, copper, plastic, brass, cast iron, stainless steel and wood
Package Type	Plastic carrying case
Set Includes	Includes ergonomic universal handle, (3) extendable blade holders (B, C, E), (8) deburring blades (B10, B20, B30, B50, B60, C40, E100, E300), plastic carrying case
Additional Information	Starter kit includes the three most popular blade types and holders for the majority of deburring applications

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement