

155-00162 Cut Sheet



Shaviv Mango IIE deburring tool set, 6 pieces, E100, E111, E120, E200 and E300, for deburring straight edges, hole edges and cross-hole both edges, rotating blade.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/155-00162>

Technical Specifications

Brand	Shaviv
Item	Deburring tool set
Series	Mango
Number of Pieces	6
Blade Type	Rotating
Ratcheting	No
Deburring Blade Manufacturer Number	E100, E111, E120, E200 and E300
For Deburring	Straight edges, hole edges and cross-hole both edges
Cutting Direction	Neutral and right hand

Application	Deburring
For Use On	Steel, aluminum, copper, plastic, brass and cast iron
Set Includes	Includes ergonomic extra-close handle, E100 deburring blade, E111 deburring blade, E120 deburring blade, E200 deburring blade, E300 deburring blade
Additional Information	E111 blade for small hole deburring down to 0.06in (1.5mm), E120 for materials with powdery chips, and E300 blade for simultaneous deburring of inner and outer bores on material up to 0.24in (6mm) thick

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement