

155-00206 Cut Sheet



Shaviv Mango II deburring tool set, 3 pieces, R20, for deburring straight edges and sheet metal, sheet metal blade.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/155-00206>

Technical Specifications

Brand	Shaviv
Item	Deburring tool set
Series	Mango
Number of Pieces	3
Blade Type	Sheet metal
Ratcheting	No
Deburring Blade Manufacturer Number	R20
For Deburring	Straight edges and sheet metal
Cutting Direction	Neutral
Application	Deburring

For Use On	Steel, aluminum, copper, plastic, brass, cast iron, stainless steel and wood
Set Includes	Includes ergonomic universal handle, extendable blade holder with hand guard, (2) R10 deburring blades
Additional Information	For heavy-duty deburring of materials with single or double straight edges up to 0.56in (14 mm) thick. holder can take two R10, R20 or R30 blades for arc-shaped finishes on workpieces up to 0.63in (16 mm) thick. handguard attached for worker safety

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement