

1550Z120BK Cut Sheet



Hammond enclosure, NEMA 1/4/4X/12/13, 171 x 121 x 55mm (HxWxD), die-cast aluminum alloy, black, powder coat finish, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1550Z120BK>

Technical Specifications

| | |
|---------------------------------|-------------------------|
| Brand | Hammond |
| Item | Enclosure |
| NEMA Rating | 1/4/4X/12/13 |
| IP Rating | IP66 |
| Enclosure Height | 171.00mm |
| Enclosure Width | 121.00mm |
| Enclosure Depth | 55.00mm |
| Cover Type | Screw cover |
| Cover Depth | 10mm |
| Integral Mounting Flange | No |
| Material | Die-cast aluminum alloy |
| Color | Black |
| Finish | Powder coat |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/1550Z120BK.pdf>
See store item page for other formats.