

1554GGY Cut Sheet



Hammond enclosure, 120 x 90 x 81mm (HxWxD), ABS plastic, RAL 7035 light gray, screw cover, purchase subpanel separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1554GGY>

Technical Specifications

Brand	Hammond
Item	Enclosure
Subpanel	Purchase subpanel separately
IP Rating	IP66
Enclosure Height	120.00mm
Enclosure Width	90.00mm
Enclosure Depth	81.00mm
Cover Type	Screw cover
Cover Depth	15mm
Integral Mounting Flange	No
Material	ABS plastic
Color	RAL 7035 light gray

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/1554GGY.pdf>
See store item page for other formats.