

# 1555D2GY Cut Sheet



Hammond enclosure, NEMA 4/4X/6/6P/12/13, 120 x 65 x 61mm (HxWxD), polycarbonate, RAL 7035 light gray, screw cover with smooth recess, purchase subpanel separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1555D2GY>

---

## Technical Specifications

|                                 |                                |
|---------------------------------|--------------------------------|
| <b>Brand</b>                    | Hammond                        |
| <b>Item</b>                     | Enclosure                      |
| <b>Subpanel</b>                 | Purchase subpanel separately   |
| <b>NEMA Rating</b>              | 4/4X/6/6P/12/13                |
| <b>IP Rating</b>                | IP68                           |
| <b>Enclosure Height</b>         | 120.00mm                       |
| <b>Enclosure Width</b>          | 65.00mm                        |
| <b>Enclosure Depth</b>          | 61.00mm                        |
| <b>Cover Type</b>               | Screw cover with smooth recess |
| <b>Cover Depth</b>              | 15mm                           |
| <b>Integral Mounting Flange</b> | No                             |
| <b>Material</b>                 | Polycarbonate                  |
| <b>Color</b>                    | RAL 7035 light gray            |

---

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None   |
| <b>UL Recognized File #</b> | None   |
| <b>UL Hazardous File #</b>  | None   |
| <b>CSA File #</b>           | None   |
| <b>RoHS Status</b>          | Meets RoHS Chemical Restrictions -<br>No CE (See RoHS Statement Below) |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a>                                 |
| <b>Other</b>                | <a href="#">RoHS Statement</a>   |