

1557HA2GY Cut Sheet



Hammond enclosure, NEMA 4/4X/6/6P/12/13, 200 x 200 x 70mm (HxWxD), polycarbonate, RAL 7035 light gray, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1557HA2GY>

Technical Specifications

Brand	Hammond
Item	Enclosure
NEMA Rating	4/4X/6/6P/12/13
IP Rating	IP68
Enclosure Height	200.00mm
Enclosure Width	200.00mm
Enclosure Depth	70.00mm
Cover Type	Screw cover
Cover Depth	56mm
Integral Mounting Flange	No
Material	Polycarbonate
Color	RAL 7035 light gray

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/1557HA2GY.pdf>
See store item page for other formats.