

# 15803B Cut Sheet



Halex fitting, zinc die cast, straight duplex, 3/8in trade size, screw clamp conduit connection. Package of 25. For use with flexible metal conduit (FMC), AC cable (BX), MC cable, (NM-B) cable. Screws and locknut included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/15803B>

## Technical Specifications

<b>Brand</b>	Halex
<b>Item</b>	Fitting
<b>Liquid-tight</b>	No
<b>Fitting Type</b>	Straight duplex
<b>Material</b>	Zinc die cast
<b>Trade Size</b>	3/8in
<b>Conduit Connection Method</b>	Screw clamp
<b>Box Connection Type</b>	1/2in male NPSM
<b>Insulation</b>	No
<b>Knockout Size</b>	1/2in
<b>Reduced Wall Flexible Metal Conduit Trade Size</b>	3/8in
<b>Flexible Metal Conduit (FMC) Compatibility</b>	Aluminum FMC, aluminum RWFC, steel FMC and steel RWFC

<b>Armored Cable (AC) Size Range</b>	Aluminum 14/2-10/3 and steel 14/2-12/4
<b>Metal Clad (MC) Cable Size Range</b>	Aluminum 14/2-10/3, steel 14/2-10/3, MCL-A 14/2-10/3 and HCF 12/2-10/2
<b>Outside Diameter</b>	0.41-0.56in
<b>Non-metallic Type B (NM-B) Cable Size</b>	With ground 14/2-12/3
<b>Quantity per Pack</b>	25
<b>For Use With</b>	Flexible metal conduit (FMC), AC cable (BX), MC cable, (NM-B) cable
<b>Includes</b>	Screws and locknut
<b>Applicable Standards</b>	UL 514B Listed

## Agency Approvals

<b>UL Listed File #</b>	E30248
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>