

1590ZGRP234BK Cut Sheet



Hammond enclosure, NEMA 4/4X, 255 x 250 x 120mm (HxWxD), fiberglass reinforced polyester, black, screw cover, purchase subpanel separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1590ZGRP234BK>

Technical Specifications

Brand	Hammond
Item	Enclosure
Subpanel	Purchase subpanel separately
NEMA Rating	4/4X
IP Rating	IP66
Enclosure Height	255.00mm
Enclosure Width	250.00mm
Enclosure Depth	120.00mm
Cover Type	Screw cover
Cover Depth	25mm
Integral Mounting Flange	No
Material	Fiberglass reinforced polyester
Color	Black

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/1590ZGRP234BK.pdf>
See store item page for other formats.