

1602-4102 Cut Sheet



ASO Safety Solutions safety contact mat, 24 x 60in, straight edge, 24 VAC/VDC operating voltage, polyurethane contact surface, black, IP65, 4.7in/120mm cable length, (1) 3-pin male M8 connector and (1) 3-pin female M8 connector.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1602-4102>

Technical Specifications

Brand	ASO Safety Solutions
Item	Safety contact mat
Size	24 x 60in
Actuation Force	150N
Response Time	< 25ms
Switching Cycles	> 1,000,000 cycles
Static Load	2000N
Edge	Straight
Operating Voltage	24 VAC/VDC
Contact Surface Material	Polyurethane
Color	Black
IP Rating	IP65
Operating Temperature	-10 to 55C
Cable Length	4.7in/120mm
Connection	(1) 3-pin male M8 connector and (1) 3-pin female M8 connector

Agency Approvals

UL Listed File #	E329422
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/1602-4102.pdf>
See store item page for other formats.