

1602-4540 Cut Sheet



ASO Safety Solutions safety contact mat, 24 x 36in, straight edge, 24 VAC/VDC operating voltage, aluminum contact surface, IP65, 4.7in/120mm cable length, (1) 3-pin male M8 connector and (1) 3-pin female M8 connector.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1602-4540>

Technical Specifications

| | |
|---------------------------------|--|
| Brand | ASO Safety Solutions |
| Item | Safety contact mat |
| Size | 24 x 36in |
| Actuation Force | 150N |
| Response Time | < 25ms |
| Switching Cycles | > 1,000,000 cycles |
| Static Load | 2000N |
| Edge | Straight |
| Operating Voltage | 24 VAC/VDC |
| Contact Surface Material | Aluminum |
| IP Rating | IP65 |
| Operating Temperature | -20 to 55C |
| Cable Length | 4.7in/120mm |
| Connection | (1) 3-pin male M8 connector and (1) 3-pin female M8 connector |

Agency Approvals

| | |
|-------------------------|--|
| UL Listed File # | E329422 |
| CE | View CE declarations |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/1602-4540.pdf>
See store item page for other formats.