


# 1602-5391 Cut Sheet



ASO Safety Solutions safety contact mat, 24 x 48in, straight edge, 24 VAC/VDC operating voltage, polyurethane contact surface, yellow, IP65, 4.7in/120mm cable length, (1) 3-pin male M8 connector and (1) 3-pin female M8 connector.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1602-5391>

## Technical Specifications

<b>Brand</b>	ASO Safety Solutions
<b>Item</b>	Safety contact mat
<b>Size</b>	24 x 48in
<b>Actuation Force</b>	150N
<b>Response Time</b>	< 25ms
<b>Switching Cycles</b>	> 1,000,000 cycles
<b>Static Load</b>	2000N
<b>Edge</b>	Straight
<b>Operating Voltage</b>	24 VAC/VDC
<b>Contact Surface Material</b>	Polyurethane
<b>Color</b>	Yellow
<b>IP Rating</b>	IP65
<b>Operating Temperature</b>	-10 to 55C
<b>Cable Length</b>	4.7in/120mm
<b>Connection</b>	(1) 3-pin male M8 connector and (1) 3-pin female M8 connector

## Agency Approvals

<b>UL Listed File #</b>	E329422
<b>UL Recognized File #</b>	N/A
<b>UL Hazardous File #</b>	N/A
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	N/A
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>