

16070074 Cut Sheet



WERMA EvoSIGNAL Mini series audible signal horn, 95 dB at 1m, 4 kHz tone frequency, continuous/pulse tone(s), 12 VAC/VDC, modular mount, ABS/polycarbonate housing, gray, IP66. Requires mounting adapter.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/16070074>

Technical Specifications

Brand	WERMA
Item	Audible signal horn
Series	EvoSIGNAL Mini
Loudness Decibel	95 dB at 1m
Tone Frequency	4 kHz
Tone Type	Continuous/pulse
Touch to Acknowledge	No
Voltage Rating	12 VAC/VDC
Mounting	Modular
Housing Material	ABS/polycarbonate
Color	Gray
IP Rating	IP66
Requires	Mounting adapter

Agency Approvals

UL Listed File #	E164155
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document