

# 16170060 Cut Sheet



WERMA EvoSIGNAL Midi series audible signal horn, 110 dB at 1m, 3.3 kHz tone frequency, (10) selectable tone(s), 115-230 VAC, modular mount, ABS/polycarbonate housing, gray, IP66. Requires mounting adapter.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/16170060>

## Technical Specifications

<b>Brand</b>	WERMA
<b>Item</b>	Audible signal horn
<b>Series</b>	EvoSIGNAL Midi
<b>Loudness Decibel</b>	110 dB at 1m
<b>Tone Frequency</b>	3.3 kHz
<b>Tone Type</b>	(10) selectable
<b>Touch to Acknowledge</b>	No
<b>Number of Alarms</b>	10
<b>Voltage Rating</b>	115-230 VAC
<b>Mounting</b>	Modular
<b>Housing Material</b>	ABS/polycarbonate
<b>Color</b>	Gray
<b>IP Rating</b>	IP66
<b>Requires</b>	Mounting adapter

## Agency Approvals

<b>UL Listed File #</b>	E164155
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/16170060.pdf>  
See store item page for other formats.