

163011 Cut Sheet



FATH leveling caster, off-white, M12-1.75, die-cast aluminum/steel/nylon/rubber, slot size 6/8/10. For use with all 1.5in, 2in, 3in, 60mm, 80mm and 90mm profile T-slotted rails. Mounting hardware included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/163011>

Technical Specifications

Brand	FATH
Item	Leveling caster
Series	10 Series, 15 Series, 30 Series, 40 Series and 45 Series
Color	Off-white
Thread Size	M12-1.75
Material	Die-cast aluminum/steel/nylon/rubber
Slot Size	6/8/10
Load Rating	1102 lb/500 kg
For Use With	All 1.5in, 2in, 3in, 60mm, 80mm and 90mm profile T-slotted rails
Includes	Mounting hardware
Requires	FATH transport/base plate with M12-1.75 threads
Manufacturer Part Number	098LF062AF65

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement