

16401.9-00 Cut Sheet



Stego enclosure heater, 20W heating capacity, PTC resistor heating element, 120-240 VAC/VDC operating voltage, 50/60 Hz, 35mm DIN rail or panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/16401.9-00>

Technical Specifications

Brand	Stego
Item	Enclosure heater
IP Rating	IP20
Heating Capacity	20W
Heating Element	PTC resistor
Operating Voltage	120-240 VAC/VDC
Hertz	50/60 Hz
Connection	12in cable with (3) 20 AWG conductors
Mounting	35mm DIN rail or panel

Agency Approvals

UL Listed File #	None
UL Recognized File #	E234324
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/16401.9-00.pdf>
See store item page for other formats.