

1701-4750 Cut Sheet



ASO Safety Solutions safety contact bumper, 60 x 100mm, 4ft length, (1) 3-pin male M8 connector and (1) 3-pin female M8 connector, 4.7in/120mm cable length. Aluminum mounting rail included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1701-4750>

Technical Specifications

Brand	ASO Safety Solutions
Item	Safety contact bumper
Size	60 x 100mm
Length	4ft
Actuation Force	150N
Switching Cycles	>10,000 cycles
Operating Voltage	24 VAC/VDC
Contact Surface Material	PVC
Operating Temperature	0 to 55 deg C
Connection	(1) 3-pin male M8 connector and (1) 3-pin female M8 connector
Cable Length	4.7in/120mm
Includes	Aluminum mounting rail

Agency Approvals

UL Listed File #	N/A
UL Recognized File #	E329422
UL Hazardous File #	N/A
CE	View CE declarations
CSA File #	N/A
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/1701-4750.pdf>
See store item page for other formats.