

172499 Cut Sheet



FATH fixed caster with lifting foot, silver/gray, 80mm diameter, aluminum/steel/TPE/thermoplastic polyurethane, slot size 8/10. For use with all 1.5in, 3in, 30mm, 40mm, 45mm, 60mm, 80mm and 90mm profile T-slotted rails.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/172499>

Technical Specifications

Brand	FATH
Item	Fixed caster with lifting foot
Series	15 Series, 30 Series, 40 Series and 45 Series
Color	Silver/gray
Size	80mm diameter
Material	Aluminum/steel/TPE/thermoplastic polyurethane
Slot Size	8/10
Load Rating	337 lb/153 kg
For Use With	All 1.5in, 3in, 30mm, 40mm, 45mm, 60mm, 80mm and 90mm profile T-slotted rails
Manufacturer Part Number	098FF080UF134110

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/172499.pdf>
See store item page for other formats.