

176104-5 Cut Sheet



IDEM micro limit switch, metal pin plunger long, (1) N.O./ (1) N.C. contact(s), snap action, 25.4mm hole spacing, polybutylene terephthalate, screw terminals. Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/176104-5>

Technical Specifications

Brand	IDEM
Item	Limit switch
Switch Type	Micro
Actuator Type	Metal pin plunger long
Contact Type	(1) N.O./ (1) N.C.
Action	Snap action
Body Width	49.2mm
Mounting Hole Spacing	25.4mm
Material	Polybutylene terephthalate
Operating Temperature	-25 to 80 deg C
Connection	Screw terminals
Quantity per Pack	5

Agency Approvals

UL Listed File #	E482215
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document