

# 176107-1 Cut Sheet



IDEM micro limit switch, metal plunger with metal roller and fixing nuts, (1) N.O./ (1) N.C. contact(s), snap action, 25.4mm hole spacing, polybutylene terephthalate, screw terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/176107-1>

## Technical Specifications

<b>Brand</b>	IDEM
<b>Item</b>	Limit switch
<b>Switch Type</b>	Micro
<b>Actuator Type</b>	Metal plunger with metal roller and fixing nuts
<b>Contact Type</b>	(1) N.O./ (1) N.C.
<b>Action</b>	Snap action
<b>Body Width</b>	49.2mm
<b>Mounting Hole Spacing</b>	25.4mm
<b>Material</b>	Polybutylene terephthalate
<b>Operating Temperature</b>	-25 to 80 deg C
<b>Connection</b>	Screw terminals

## Agency Approvals

<b>UL Listed File #</b>	E482215
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>