

176112-1 Cut Sheet



IDEM micro limit switch, lever hinge with steel roller, (1) N.O./ (1) N.C. contact(s), snap action, 25.4mm hole spacing, polybutylene terephthalate, screw terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/176112-1>

Technical Specifications

| | |
|------------------------------|-------------------------------|
| Brand | IDEM |
| Item | Limit switch |
| Switch Type | Micro |
| Actuator Type | Lever hinge with steel roller |
| Contact Type | (1) N.O./ (1) N.C. |
| Action | Snap action |
| Body Width | 49.2mm |
| Mounting Hole Spacing | 25.4mm |
| Material | Polybutylene terephthalate |
| Operating Temperature | -25 to 80 deg C |
| Connection | Screw terminals |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E482215 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/176112-1.pdf>
See store item page for other formats.