

19RL-401 Cut Sheet



Sifam Tinsley AC current transformer, solid core, 400 A primary, 5 A secondary, 4.25 in diameter sensing window, $\pm 1\%$ accuracy, (2) 24 in 16 AWG lead wires.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/19RL-401>

Technical Specifications

Brand	Sifam Tinsley
Item	Transformer
Transformer Type	Current
Voltage Type	AC
Body Type	Solid core
Primary Current	400 A
Secondary Current	5 A
Sensing Window	4.25 in diameter
Accuracy	$\pm 1\%$
Secondary Connection Type	(2) 24 in 16 AWG lead wires
Mounting	Pass-through conductor
Additional Information	Metering Class Accuracy achievable when maximum burden values are not exceeded

Agency Approvals

UL Listed File #	None
UL Recognized File #	E472409
UL Hazardous File #	None
CE	View CE declarations
CSA File #	N/A
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/19RL-401.pdf>
See store item page for other formats.