

1PU06MC40 Cut Sheet



NITRA pneumatic coiled tubing, ether-based polyurethane, clear blue, 6mm outside diameter, 5/32in (4mm) inside diameter, 40 coils, 8.4ft (2.56m) working length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1PU06MC40>

Technical Specifications

Brand	NITRA
Item	Coiled tubing
Working Fluid	Air or inert gas
Material	Ether-based polyurethane
Color	Clear blue
Outside Diameter	6mm
Inside Diameter	5/32in (4mm)
Number of Coils	40
Working Length	8.4ft (2.56m) working length
Operating Pressure	180 psi
Operating Temperature	-40 to +160 deg F

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document