

# 1PU08MC10 Cut Sheet



NITRA pneumatic coiled tubing, ether-based polyurethane, clear blue, 5/16in (8mm) outside diameter, 5mm inside diameter, 10 coils, 3.3ft (1.01m) working length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1PU08MC10>

## Technical Specifications

<b>Brand</b>	NITRA
<b>Item</b>	Coiled tubing
<b>Working Fluid</b>	Air or inert gas
<b>Material</b>	Ether-based polyurethane
<b>Color</b>	Clear blue
<b>Outside Diameter</b>	5/16in (8mm)
<b>Inside Diameter</b>	5mm
<b>Number of Coils</b>	10
<b>Working Length</b>	3.3ft (1.01m) working length
<b>Operating Pressure</b>	175 psi
<b>Operating Temperature</b>	-40 to +160 deg F

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>