

1PU10MC10 Cut Sheet



NITRA pneumatic coiled tubing, ether-based polyurethane, clear blue, 10mm outside diameter, 6.5mm inside diameter, 10 coils, 4.0ft (1.22m) working length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1PU10MC10>

Technical Specifications

Brand	NITRA
Item	Coiled tubing
Working Fluid	Air or inert gas
Material	Ether-based polyurethane
Color	Clear blue
Outside Diameter	10mm
Inside Diameter	6.5mm
Number of Coils	10
Working Length	4.0ft (1.22m) working length
Operating Pressure	150 psi
Operating Temperature	-40 to +160 deg F

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document